

Model M 53 | Drying and heating chambers Classic.Line with forced convection and advanced program functions

With a maximum of 300 °C and various programming options the M series material test chambers are ideal for material and aging tests. With a high air flow, the powerful fans ensure rapid heating.

BENEFITS

- Uniform drying conditions thanks to APT.line[™] technology
- · Identical test conditions throughout the chamber interior independent of sample size and quantity
- · Outstanding thermal insulation saves operation costs
- · Advanced programming options



Model 53



Model 53

MAIN FEATURES

- Temperature range: room temperature plus 5 °C to 300 °C
- APT.line[™] preheating chamber technology
- · Adjustable fan speed
- Program-controlled ventilation flap
- · Color LCD controller with time-segment programming
- · 2 chrome-plated racks
- Class 2 independent adjustable temperature safety device (DIN 12880) with visual alarm
- Computer interface: RS 422

ORDERING INFORMATION

Interior volume [cu.ft.]	Voltage	Option model	Version	ArtNo.
Model M 53				
1.9	230 V 1 ph 50/60 Hz	Standard	M053-230V	9010-0201




TECHNICAL DATA

Description	M053-230V ¹
Article Number	9010-0201
Performance Data Temperature	
Temperature range 5 °C above ambient temperature to [°C]	300
Temperature variation at 150 °C [± K]	1.3
Temperature fluctuation at 150 °C [± K]	0.3
Heating-up time to 150 °C [min]	15
Recovery time after 30 seconds door open at 150 °C [min]	3
Air change data	
Air change (approx.) at 150 °C [x/h]	192
Electrical data	
Rated Voltage [V]	230
Power frequency [Hz]	50/60
Nominal power [kW]	1.2
Phase (Nominal voltage) [ph]	1
Outer dimensions	
Width net [mm]	635
Height net [mm]	780
Depth net [mm]	575
Wall clearance back [mm]	160
Wall clearance sidewise [mm]	100
Internal Dimensions	
Width [mm]	400
Height [mm]	400
Depth [mm]	340
Measures	
Interior volume [L]	53
Net weight of the unit (empty) [kg]	61
permitted load [kg]	40
Load per rack [kg]	15
Environment-specific data	
Energy consumption at 150 °C [Wh/h]	300
Fixtures	
Number of shelves (std./max.)	2/5

¹ All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS incl. fittings and connections [mm]





OPTIONS AND ACCESSORIES

Designation	Description	*	ArtNo.
	back		
	10 mm	01	8012-1287
	30 mm	01	8012-137
	50 mm	01	8012-1387
	left		
	10 mm	01	8012-128
	30 mm	01	8012-136
	50 mm	01	8012-137
Access port with silicone	100 mm	01, 11	8012-151
blug	right		
	10 mm	01	8012-127
	30 mm	01	8012-135
	50 mm	01	8012-137
	100 mm	01, 11	8012-150
	top		
	10 mm	01	8012-126
	30 mm	01	8012-136
	50 mm	01	8012-138
Analog output 4-20 mA	for temperature values (output not adjustable)	-	8012-048
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-112
	for temperature, measurement in center of chamber at specified temperature	-	8012-114
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-160
emperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-158
	temperature measurement incl. certificate, 9 measuring points at specified temperature	_	8012-155
Cart	Cart – stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm	_	9051-001
Data Logger Kit	T 350: For continuous temperature logging from 0 °C to 350 °C; kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	19	8012-071
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	19	8012-082
Door gasket	made of FKM, silicone-free	03	8012-130
Door lock	lockable door handle	-	8012-125
Gas-tight option model	incl. additional measures for gas containment	09	8012-018
HEPA air filter	On fresh air supply for unit; filter classification H14 (acc. to. EN 1822-1:2009, > 99.995% at 0.3 µm)	-	8012-022
nert gas connection	with gas inlet and outlet, Ø 10 mm, incl. additional measures to provide the greatest possible impermeability to gas	_	8012-154
	RS 422 cable set and RS 232 / RS 422 interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	_	8012-055
	230 V, 50/60 Hz option model	_	8012-055
Interface converter	RS 422 cable set and RS 422 / Ethernet interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	_	8012-040
	230 V, 50/60 Hz option model	_	8012-038
nterface converter,	RS 422 cable set and RS 422 / USB interface converter for connection to 10-way plug distributor or for connection		0040.000
JSB / RS422	to a unit (USB-powered converter)	_	8012-066
Lockable controller keyboard	Lockable controller keyboard with key-operated switch	-	8012-052
Measurement of air	in accordance with ASTM D5374, definition and protocol according to ambient temperature	-	8012-119
exchange rate			
exchange rate oH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-001

^{*} Notes > See last page



Designation	Description	*	ArtNo.
Rack	chrome plated		6004-0002
	stainless steel	-	6004-0007
Rack accessories	Rack accessories – fasteners (1 set of 4) for additional security of racks	-	8012-0531
RS 422 interface	modular plug distributor for 10 RS 422 interfaces	-	8012-0295
RS 422 interface, cable (15 m)	RS 422 connection cable (15 m) between plug distributor and RS 422 interface	-	5023-0036
RS 422 interface, cable (50 m)	RS 422 extension cable (50 m) between interface converter and unit or RS 232 / RS 422 plug distributor	-	5023-0117
Rubber pads	set of 4 anti-slip feet, for safe stacking of unit	10	8012-0001
Shelf, perforated	Stainless steel	-	6004-0029
Software	APT-COM™ communications software		
	version 2 to 3, GLP edition	19	9053-0016
	version 3, BASIC edition	19	9053-0014
	version 3, GLP edition	19	9053-0015
	version 3, STANDARD edition		9053-0013
	APT-COM™ communications software, price: for free		
	version 3, GLP DEMO Edition	19	9053-0008
Viewing window and interior lighting	viewing window in door, 230 x 230 mm,		
	230 V option model	-	8012-0055

^{*} Notes > See last page

SERVICES

Designation	Description	*	ArtNo.
Installation services			
Data Logger Kit installation service	unit function instructions for operation and programming of the controller	18	DL10-0600
Installation	and set up of unit at operating location, connect to existing connections	13, 18	DL10-0100
Preventive maintenance			
Preventive maintenance	Executive of equipment inspection according to maintenance plan	14, 18	DL20-0200
Calibration services			
Calibration temperature incl. certificate	including certificate, one measuring point in center of chamber at specified temperature	14, 16, 17, 18	DL30-0101
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	14, 16, 17, 18	DL33-0000
Temperature measurement 18 measuring points	including certificate, 18 measuring points at specified temperature	14, 16, 17, 18	DL30-0118
Temperature measurement 27 measuring points	including certificate, 27 measuring points at specified temperature	14, 16, 17, 18	DL30-0127
Temperature measurement 9 measuring points	including certificate, 9 measuring points at specified temperature	14, 16, 17, 18	DL30-0109
Validation services			
Execution of IQ/OQ	in accordance with qualification folder	15, 18, 20	DL41-0200
Execution of IQ/OQ/PQ	in accordance with customer's requirement, price: on request	15, 18	DL44-0500
Qualification folder IQ/OQ	supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001	15, 18, 20	8012-0862
Qualification folder IQ/OQ/PQ	supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ	15, 18	8012-0950
Warranty service			
Extension of the warranty from 2 to 3 years	beginning with the date of delivery, wearing parts are not included	-	DL01-0041
Extension of the warranty from 2 to 5 years	beginning with the date of delivery, wearing parts are not included	-	DL01-0042

^{*} Notes > See last page



NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used. Heat resistant only to max. 200 °C. 01 02
- 03
- Only available on units rated for 230 V.
- Heating-up time may increase as a result of the lower heat conductivity.
- The additional heat input may affect the temperature behavior.
- Not in conjunction with the optional access port, door with window and interior lighting. 09
- Not available on 23-liter units.
- Not available on 23- or 53-liter units.
- 10 11 12 Only available on units rated for 230 V or 400 V.
- Installation and connections take place at unit location; transport within the company only upon consultation.
- We recommend a BINDER service contract to cover unit inspections, calibrations and validations.
- OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory.
- 17
- Calibration is performed according to the BINDER factory standard.

 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter.
- When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items.

When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.